
## ANEMOSTAT® AIR TERMINAL CONTROLS

SD-D-J029

- SINGLE DUCT
- DIRECT DIGITAL CONTROLS BY JOHNSON CONTROLS
- DDC SUPPLIED TO FACTORY FOR INSTALLATION

• ELECTRIC HEAT - STEP CONTROL



## **IMPORTANT!**

- 1. THE 24 VAC SOURCE IS LOCATED IN HEATER ENCLOSURE AND IS SIZED TO HANDLE HEATER CONTACTOR LOAD + 15VA OVERHEAD FOR CONTROLLER AND ACTUATOR.
- 2. CONSULT CONTROLS DOCUMENTATION FOR DETAILS AS INSTALLED HARDWARE WILL VARY FROM THAT SHOWN.

FACTORY WIRING
FIELD WIRING
FACTORY PIPING

JOB NAME: SUBMITTED BY:

DATE:

DWG #: SD-D-J029

REV: -

DATE: 3-23-2017